

Innovators in 3D printing



Technical Data Sheet

Polymaker PC-ABS

www.polymaker.com



Polymaker[™] PC-ABS is a PC/ABS polymer blend which offers excellent toughness and heat resistance while displaying good surface finish and good compatibility with metal plating.

PHYSICAL PROPERTIES

Property	Testing Method	Typical Value
Density	ISO1183, GB/T1033	1.1 g/cm ³ at 21°C
Melt Index	260°C, 5 kg	11-17 g/10min
Light Transmission	N/A	N/A
Flame retardancy V2	UL94	V2

CHEMICAL RESISTANT DATA

Property	Testing Method
Effect of weak acids	Not Resistant
Effect of strong acids	Not Resistant
Effect of weak alkalis	Slight Resistant
Effect of strong alkalis	Not Resistant
Effect of organic solvent	Not Resistant
Effect of oils and grease	No data available
Effect of Sunlight	No data available

MOISTURE ABSORPTION CURVE



THERMAL PROPERTIES

Property	Testing Method	Typical Value
Glass transition	DSC, 10°C/min	109 °C
Melting temperature	DSC, 10°C/min	N/A
Crystallization temperature	DSC, 10°C/min	N/A
Decomposition temperature	TGA, 20°C/min	N/A
Vicat softening temperature	ISO 306 GB/T 1633	135 °C
Heat deflection temperature	ISO 75 1.8MPa	106.4 °C
Heat deflection temperature	ISO 75 0.45MPa	111.7 °C
Thermal conductivity	N/A	N/A
Heat shrinkage rate	N/A	N/A

HDT CURVE



Polymaker[™] PC-ABS

0.45Mpa 1.8Mpa

MECHANICAL PROPERTIES

Property	Testing Method	Typical Value
Young's modulus (X-Y)		1835 ± 65 MPa
Young's modulus (Z)	ISU 927, GB/T TU40	2297 ± 113 MPa
Tensile strength (X-Y)	ISO 527, GB/T 1040	39.9 ± 1.0 MPa
Tensile strength (Z)		40.0 ± 2.2 MPa
Elongation at break (X-Y)		4.2 ± 0.3 %
Elongation at break (Z)	130 327, GD/1 1040	3.3 ± 0.9 %
Bending modulus (X-Y)		2081 ± 106 MPa
Bending modulus (Z)	130 170, GD/1 9341	N/A
Bending strength (X-Y)		66.3 ± 0.9 MPa
Bending strength (Z)	130 170, GD/1 9341	N/A
Charpy impact strength (X-Y)		25.8 ± 1.3 kj/m ²
Charpy impact strength (Z)	130 179, GD/1 9343	N/A
Low temperature impact	ISO 179-1/1eA:2010,	13 ± 2 kj/m ²
strength (X-Y)	-30°C	
Low temperature impact	ISO 179-1/1eA:2010,	1.5 ± 0.2 kj/m ²
strength (Z)	-30°C	

HOW TO MAKE SPECIMENS

Printing temperature	260 °C
Bed temperature	110 °C
Shell	2
Top & bottom layer	4
Infill	100%
Environmental temperature	90 – 100 (recommended) (°C)
Cooling fan	OFF

Note:

- When printing with Polymaker[™] PC-ABS it is recommended to use an enclosure. For large part it is recommended to use a heated chamber.
- It is recommended to anneal the printed part right after the printing process to release the residual internal stress. Annealing settings: 90°C for 2h

TENSILE TESTING SPECIMEN

ASTM D638 (ISO 527, GB/T 1040)



DISCLAIMER:

The typical values presented in this data sheet are intended for reference and comparison purposes only. They should not be used for design specifications or quality control purposes. Actual values may vary significantly with printing conditions. End- use performance of printed parts depends not only on materials, but also on part design, environmental conditions, printing conditions, etc. Product specifications are subject to change without notice.

Each user is responsible for determining the safety, lawfulness, technical suitability, and disposal/ recycling practices of Polymaker materials for the intended application. Polymaker makes no warranty of any kind, unless announced separately, to the fitness for any use or application. Polymaker shall not be made liable for any damage, injury or loss induced from the use of Polymaker materials in any application.