Version 1.4

Facilan™ C8


Facilan™ C8 is the first product of our Facilan™ family. End use industrial parts and consumer friendly printed parts as well as high end prototypes for business are the applications areas for C8. The first Fifth Generation 3D printing material, Facilan™ C8 has better mechanical qualities, best surface quality and high tolerances that combine to make a material suited for high throughput and high repeatability production in Additive Manufacturing.


MATERIAL PROPERTIES	TYPICAL VALUE	TEST METHOD
Density	1.4 g/cm ³	ISO 1183-1
Tensile Strength	45 MPa	ISO 527-1*
Elongation at yield	4 %	ISO 527-1*
Tensile Modulus	3000 MPa	ISO 527-1*
Flexural Strength	65 MPa	ISO 178
Flexural Modulus	3650 MPa	ISO 178
Izod impact strength (notched)	7 kJ/m²	ISO 180-1
Shore D Hardness	72	ISO 868
Heat Deflection Temperature	55°C	ISO 75 B**
*T 1		

^{*}Tensile sample thickness 1.5 mm

^{** 120} K/h

PRINT RECOMMENDATIONS	
Nozzle Temperature	180 - 210 °C
Bed Temperature	25 - 50 °C
Print Speed	40 - 70 mm/s
Bed Adhesion	PEI Sheet / Glass





Disclaimer: ElogioAM makes no warranties what so ever, either expressed or implied, including but not limited to, any implied fitness for any particular purpose. From the moment the product is shipped it is beyond our control. The information in this document is believed to be correct at the time of writing. However, handling, processing, settings, the type of 3D printer, slicing and other variables are completely up to the user. The method through which the product is used can be varied. It is up for the customer to determine how it is 3D printed and whether it is fit for purpose or suited to a particular application.

Printer : Ultimaker 2Nozzle temp : 200°C

■ Bed temp : 50°C
■ Infill : 100%

Layerheight: 0.1 mmPrint speed: 50 mm/sWall thickness: 0.7 mm

Wall line count: 2

Additional info: For many 3D printers, C8 will print best at approximately 200°C with a bed temperature of 50°C and a speed of 50 mm/s. In designs with significant overhangs and bridges, best results are obtained with fans at 80%. If your model has no overhangs then putting your fans at 0% improves interlayer bonding and in so doing the final mechanical strength of your part. To get the best results while printing we advise you to keep the 3D printer in a room where there is hardly any draft and/or temperature fluctuations. Keep the 3D printer out of direct sunlight. When the 3D printer is not being used it is important to keep the ElogioAM Facilan™ C8 filament in a bag and stored in a cool, dry and dark place until it is used again.

Info@ElogioAM.com | ElogioAM.com | Waarderweg 56, 2031 BP Haarlem | The Netherlands

